

CIBA VISION® O₂ OPTIXTM \$14.75 **FOCUS® NIGHT & DAY®** \$42.95 FRESHLOOK® COLORS \$23.95 FRESHLOOK® COLORBLENDS® \$23.95 FRESHLOOK® ONE-DAY™ (10 Pack) \$9.95 FRESHLOOK® RADIANCE™ \$23.95 FRESHLOOK® DIMENSIONS™ \$23.95 FRESHLOOK® COLORBLENDS® TORIC \$40.95 FRESHLOOK® HANDLING TINT \$14.45 **FRESHLOOK® TORIC** \$32.95 FOCUS® DAILIES® (30 Pack) \$12.75 FOCUS® DAILIES® (90 Pack) \$33.95 FOCUS® DAILIES® PROGRESSIVES (30 Pack) \$17.45 FOCUS® DAILIES® TORIC (30 Pack) \$17.45 **FOCUS® 1-2 WEEK** \$14.25 FOCUS® 1-2 WEEK SOFTCOLORS® \$23.75 **FOCUS® MONTHLY** \$22.50 \$33.75 FOCUS® MONTHLY SOFTCOLORS® **FOCUS® TORIC** \$38.95 **FOCUS® PROGRESSIVES** \$26.95 PRECISION® UV \$14.75 CIBASOFT® SOFTCOLORS® (MTO \$55.95) \$32.95 CIBASOFT® STANDARD™ (STD) VISITINT® \$22.45 CIBASOFT® VISITINT® (MTO \$48.95) \$20.45 \$36.95 CSI® LOCATOR TINT (MTO \$61.95) **CSI® FLEXIBLE WEAR (MTO)** \$59.95 CSI® TORIC (MTO) \$89.95 DURASOFT® 2 LITETINT® (MTO \$47.95) \$21.75 **DURASOFT® 2 COLORS FOR LIGHT EYES** (MTO \$79.95) \$34.95 DURASOFT® 2 OPAQUE® (MTO \$87.95) \$36.95 **DURASOFT® 2 COLORBLENDS™** (MTO \$87.95) \$36.95 **DURASOFT® OPTIFIT® 2 TORIC** (MTO) \$65.95 **DURASOFT® OPTIFIT® 2 TORIC COLORS** (MTO) \$94.95 **DURASOFT® 3 LITETINT®** (MTO \$51.95) \$24.45 **DURASOFT® 3 OPAQUE** (MTO \$88.95) \$60.95 **DURASOFT® 3 COMPLEMENT®** (MTO \$88.95) \$60.95 DURASOFT® 3 COLORBLENDS® (MTO \$88.95) \$60.95 **DURASOFT® OPTIFIT® 3 TORIC** (MTO) \$76.95 **DURASOFT® OPTIFIT® 3 TORIC UV (MTO)** \$94.95 **DURASOFT® OPTIFIT® 3 TORIC COLORS** (MTO) \$94.95 HYDROCURVE® II (MTO) \$90.95 \$117.95 HYDROCURVE® APHAKIC (MTO) \$83.95 **HYDROCURVE® 3 TORIC** (MTO) ILLUSIONS® OPAQUE (MTO \$82.95) \$45.95

COOPERVISION®	
BIOMEDICS® 38	\$14.95
BIOMEDICS® 55	\$12.95
BIOMEDICS® 55 PREMIER	\$12.95
BIOMEDICS® 1 DAY (90 Pack)	\$36.95
MINI™	\$49.95
PROACTIVE® 55 EW	\$17.95
ZERO 4° SOFBLUE°	\$25.95
ZERO 6° SOFBLUE°	\$23.95
FREQUENCY® 55 EW	\$11.95
FREQUENCY® 38	\$12.95
FREQUENCY® 55 ASPHERIC	\$11.95
FREQUENCY® 55 TORIC	\$34.95
FREQUENCY® 55 TORIC XR	\$62.95
EXPRESSIONS™ OPAQUE	\$22.95
EXPRESSIONS™ ACCENTS	\$22.95
NATURAL TOUCH® OPAQUE	\$39.75
PREFERENCE® STANDARD (4 Pack)	\$44.95
PREFERENCE® FW (4 Pack)	\$44.95
PREFERENCE® TORIC (4 Pack)	\$77.95
PREFERENCE® TORIC XR (4 Pack)	\$99.95
PROCLEAR COMPATIBLES®	\$24.45
VANTAGE® DW (Handling Tint)	\$46.25
VANTAGE THIN® FW (Handling Tint)	\$46.25
VERTEX SPHERE™	\$12.95
VERTEX TORIC™	\$19.95
VERTEX TORIC™ XR	\$41.95
COOPER CLEAR™ DW/FW	\$23.95
COOPER TORIC™	\$37.95
SILVER 07	\$10.95

JOHNSON & JOHNSON®	
ACUVUE® 2	\$13.50
ACUVUE® 1 DAY (30 Pack)	\$18.95
ACUVUE® MOIST 1 DAY (30 Pack)	\$18.95
ACUVUE® ADVANCE™	\$16.95
ACUVUE® OASYS™	\$19.95

HYDROGEL VISION®	
EXTREME H2O® 59	\$14.95
EXTREME H20® 59 XTRA	\$14.95
EXTREME H2O® 54	\$14.95



WILDEYES®

SOFTMATE® B (MTO \$47.95)

SOFTMATE® II (MTO \$50.95)
TORISOFT® TORIC (MTO \$81.95)



\$21.95 \$23.95

\$59.95

\$35.95



BAUSCH & LOMB®	
PUREVISION™	\$26.95
PUREVISION™ TORIC	\$29.95
PUREVISION™ MULTI-FOCAL	\$32.95
SOFLENS™ 38	\$12.45
SOFLENS™ 59	\$8.25
SOFLENS™ 66 TORIC	\$18.95
SOFLENS™ MULTI-FOCAL	\$29.95
SOFLENS™ ONE DAY (90 Pack)	\$34.95
OPTIMA™ SP (2 Blister Pack)	\$26.95
OPTIMA™ TORIC (Two Pack \$125.95)	\$71.95
H3/H4 (HIGH PLUS)	\$104.95
SILSOFT™ APHAKIC	\$125.95
NIKE MAXSIGHT™	\$31.95

SOLUS™	
SOLUS TCL [™] Single Vial (Tier 2 \$59.95)	\$49.95
SOLUS TCL™ 4 Pack (Tier 2 \$99.95)	\$89.95
SOLUS 55A™	\$8.95

DaVinci SUPPLEMENTS	`
HEALTHY EYES™ (90 Capsules)	\$18.00
OMEGA-3 1000™ (90 Capsules)	\$11.95
CoQsol® (60 Capsules)	\$16.50
LUTEIN (60 Capsules)	\$7.70
GINKGO BILOBA (90 Capsules)	\$5.80
SPECTRA™ (120 Tablets)	\$10.75

SHIPPING RATES	
US POSTAL (3-7 Days)	\$3.50
GROUND COURIER (2-5 days)	\$4.85
2ND DAY Add \$20 for Saturday delivery	\$8.95
OVERNIGHT Add \$20 for Saturday delivery	\$14.95
UP TO 3 POUNDS Within the Continen	tal US only

TO OPEN YOUR NEW IMPERIAL OPTICAL STRATEGIC PARTNER ACCOUNT TODAY, COMPLETE THE NEW ACCOUNT FORM BELOW AND FAX TO 800-803-0455.

FULL LEGAL NAME		D/B/A BUSINESS NAME		
BILLING ADDRESS		CITY	STATE	ZIP
*SHIPPING ADDRESS (IF DIFFERENT I	FROM BILLING)	CITY	STATE	ZIP
PHONE NO.	FAX NO.	E-MAIL	WEB SITE	
YEAR BUSINESS ESTABLISHED	NO. OF EMPLOYEES	FEDERAL TAX ID		
☐ Proprietorship	☐ Partnership	☐ Corporation	☐ Limited Liability	Corp
Communication Preference:	☐ Fax	☐ Telephone	☐ Regular Mail	☐ E-Mail
* IF MULTIPLE SHIP TO LOCATIONS I	Please provide on separate docu	JMENT.		
credit. Proprietorship, partnership, a	nd personal guarantor applicants und	to release any information necessary to erstand that Imperial Optical Inc. may review of existing or future extension:	order a consumer credit report in	
and all additional documents, finance		ment represent and warrant that the i rnished by applicant to Imperial Optica misleading.		
AUTHORIZED SIGNATURE		DATE		









TORIC CLISTOM LENS

The Solus™ TCL is a Soft Back Surface Toric Lens for Daily Wear

The **Solus™TCL** toric custom lens is designed for correction of corneal and residual astigmatism. **Solus™TCL** combines the base curve design of soft back surface toric lenses with computer-controlled lathing that generates a lenticulated front surface. The result is a reduction in the amount of lens material, improved stabilization and excellent visual acuity.

Produced from a new generation of GMMA + VP soft lens material, the lens allows increased moisture retention during wear and is resistant to deposits. **Solus™TCL** lenses are manufactured with a blue visibility tint for easy handling and are packaged in single-lens vials and 4-vial economy packs.

Lens Material: Acofilcon A

The lens material GM3 is a terpolymer based on a high purity Glycerol Methacrylate 2, 3-Dihydroxypropyl Methacrylate (GMA). Manufactured with a blue visibility/handling tint. When hydrated, the lens consists of 42% Acofilcon A and 58% water by weight when immersed in normal saline.

Fitting Procedure

Solus™TCL is easy to fit empirically with a high success rate. The lens is stabilized by adding ballast to the front, maintaining the cylinder in the base curve. A "dot" is engraved at six o'clock to assist in calculating alignment of the lens.

Recommended Wearing Schedule

Solus™TCL lenses are designed for daily wear on a 3-month replacement schedule.

Cleaning

Hydrogen peroxide or a chemical disinfecting system (MPS) is recommended for cleaning the lens.

Lens Properties

Water Content	Tensile Strength	Refraction Index (wet)	Oxygen Permeability (DK - Fatt scale)
58% in saline at 20°C	6.61 kg/cm ²	1.39	22 x 10 ⁻¹¹ at 35°C

Lens Parameters

Diameter 13.5 mm, 14.5 mm* and 15.0 mm	Posterior Curve Toric with blended peripheral curves	Front Curve Lenticulated with prism ballast (varies with power)
Power Range +20.0 D to -20.0 D	Nominal Centre Thickness 0.19 mm at -3.00 D	Base Curve Range 8.10 mm to 9.30 mm (in 0.3 mm steps) 8.4 mm*, 8.7 mm*, 9.0 mm*
Cylinders -0.25 D to -10.00 D	Axis 0° to 180° in 1° steps	Optical Zone Diameter 8.00 mm at -3.00 D (varies with power, sphere and cylinder)

Note: Matching sphere lenses available.





^{*} Stock lenses





Enhanced Vision

- > Advanced aspheric optical design provides excellent performance to enhance vision.
- > UV blocking protects from the harmful effects of ultraviolet light.

Predictable and Reproducible Quality

- > Truform[™] cast molding process ensures consistent high quality, thin, smooth, lens to lens reproducibility.
- > Unique lens design improves comfort by reducing unnecessary thickness in the lens by incorporating a pressure relieving edge lift to reduce any scleral indentation.
- > ISO 9001:2000 and ISO 13485:2003 certified facilities.

Convenience


- > Easy to handle for both the experienced and first-time wearers.
- > The design assists with correct lens orientation to minimize chances of inverted lens insertion.

High Patient Satisfaction


Lens Specifications

- > Results from an extensive clinical study* showed equivalence of the Solus™55a to three leading lens brands in vision, comfort and handling.
- > 56% of the wearers preferred **Solus™55a** versus the other brands.
- > Those wearers selecting the **Solus™55a** as their preference were 5 times more likely to purchase the lens over any other brand.


Lens Comfort



Lens Handling



Overall Performance





* Data on file

Material	Lens Design	Handling Tint
45% methafilcon A, 55% water	Tangential flat back edge, reducing aspheric front optic	Light Blue
Base Curve	Diameter	Power Range
8.70 mm (Single fit)	14.5 mm	-12.00 to +6.00 (steps: 0.50D > +4.50 & -6.50
Wear Indication	Nominal Centre Thickness**	DK @ 35°C
Daily Wear	0.09 mm	$18.8 \times 10^{-11} \text{ (cm}^2\text{/s)(mIO}_2\text{/ml.mm Hg)}$
Pack Size	Diagnostic Lenses	
6 lenses	Single Blisters	

^{**-3.00} D lens









IMPERIAL OPTICAL NOW OFFERS VALUE-PRICED, QUALITY FRAMES

These frames, all at under \$10.00, provide you with a high-margin return on your "economy" frame selection for cost-conscious patients. No minumum order required. If you are not satisfied with the quality, we will refund your purchase price, no questions asked (when you return the frames within 30 days).

24-PIECE STARTER KIT FOR \$149

INCLUDES 8 DIFFERENT STYLES AVAILABLE IN 3 COLORS EACH

